

STANDARD CHARGING CABLE

FOR SAFE CHARGING OF ELECTRIC AND HYBRID VEHICLES



THE STANDARD CHARGING CABLE FROM LAPP

enables quick and easy charging at public charging stations and wallboxes. The high protection class IP55, together with the additional longitudinal watertightness, ensures excellent moisture protection. The charging cable, designed according to the latest IEC and EN standards, is robust and durable.

ADVANTAGES AT A GLANCE

- Silver-plated contacts for safe power transmission and durability
- Meets all relevant IEC and EN product requirements
- Improved ergonomic, robust plug/coupling design
- For all electric cars and plug-in hybrids with type 2 vehicle socket
- LAPP quality, developed and manufactured in Europe

WITH YOUR COMPANY
LOGO ON REQUEST

ERGONOMIC
HANDLE

SILVER PLATED
CONTACTS

IN YOUR COMPANY
COLOURS ON REQUEST



INCLUDED IN DELIVERY

- Charging cable with dust cap
- User manual

APPLICABLE STANDARDS

- IEC 62196-1:2022
- IEC 62196-2:2022
- IEC 61851-1:2023
- IEC 62893-1:2017
- DIN EN 17186:2019
- 2011/65/EU (RoHS)
- 2014/35/EU (LVD)

TECHNICAL INFORMATION

- Charging mode: mode 3 acc. to IEC 61851
- Connections: Type 2 on both sides acc. to IEC 62196
- Rated current: see variant table
- Rated voltage: see variant table
- Charging power: see variant table
- Permissible temperature range: -40°C to +50°C
- Cable type: ÖLFLEX® CHARGE
- Cable length: see variant table
- Protection class: IP55 with additional longitudinal watertightness
- Halogen free
- Flame retardant
- Oil resistant

STANDARD CHARGING CABLE

FOR SAFE CHARGING OF ELECTRIC AND HYBRID VEHICLES

CABLE VARIANTS

Item number	Power	Cable length	Cable type	Colour	Phases	Current	Weight (kg)
5555934032	22kW	10m	straight	black	3	32A	5.24
5555931037	22kW	10m	straight	orange	3	32A	5.24
5555934007	22kW	7m	straight	black	3	32A	3.89
5555934031	22kW	7m	straight	orange	3	32A	3.89
5555934003	22kW	5m	straight	black	3	32A	3.01
5555934027	22kW	5m	straight	orange	3	32A	3.01
5555934041	22kW	3m	straight	black	3	32A	2.20
5555934040	22kW	3m	straight	orange	3	32A	2.20
5555934050	11kW	10m	straight	black	3	20A	3.01
5555934049	11kW	10m	straight	orange	3	20A	3.01
5555934005	11kW	7m	straight	black	3	20A	2.30
5555934029	11kW	7m	straight	orange	3	20A	2.30
5555934001	11kW	5m	straight	black	3	20A	1.85
5555934025	11kW	5m	straight	orange	3	20A	1.85
5555934052	11kW	3m	straight	black	3	20A	1.43
5555934051	11kW	3m	straight	orange	3	20A	1.43
5555934068	7.4kW	10m	straight	black	1	32A	4.26
5555934064	7.4kW	10m	straight	orange	1	32A	4.26
5555934006	7.4kW	7m	straight	black	1	32A	2.63
5555934030	7.4kW	7m	straight	orange	1	32A	2.63
5555934002	7.4kW	5m	straight	black	1	32A	2.08
5555934026	7.4kW	5m	straight	orange	1	32A	2.08
5555934067	7.4kW	3m	straight	black	1	32A	1.90
5555934063	7.4kW	3m	straight	orange	1	32A	1.90
5555934066	3.7kW	10m	straight	black	1	20A	2.49
5555934062	3.7kW	10m	straight	orange	1	20A	2.49
5555934004	3.7kW	7m	straight	black	1	20A	1.63
5555934028	3.7kW	7m	straight	orange	1	20A	1.63
5555934000	3.7kW	5m	straight	black	1	20A	1.35
5555934024	3.7kW	5m	straight	orange	1	20A	1.35
5555934065	3.7kW	3m	straight	black	1	20A	1.28
5555934061	3.7kW	3m	straight	orange	1	20A	1.28

Note: other cable variants and options on request

Please scan or click
for more information:



Lapp Mobility GmbH
Oskar-Lapp-Str. 2 · D-70565 Stuttgart
Phone: +49 711 7838 - 04 · Fax: +49 711 7838 - 3520
www.lappmobility.com · info.de.lmd@lapp.com

