



Intelligence charging.
Future driving.
Easiness growing.

alive BY  **LAPP**

HIGH POWER DC CHARGING CABLE

With CCS2 plug incl. exchangeable mating face



VARIANTS

300A continuous | 500A Boost Mode
250A continuous | 500A Boost Mode
200A continuous | 350A Boost Mode

TECHNICAL DETAILS

Ambient temperature (operation)	-30°C to +50°C
Degree of protection	IP44 mated
Rated voltage for power contacts	1000V
Standards/regulations	IEC 62196-3, VDE-certified
Temperature sensor	One for each power contact

KEY FEATURES

Boost mode up to **500kW**
Power consumption measurement
Uncooled (without liquid)
Exchangeable mating face
Untouchable contacts
Weight and size optimized
Designed and manufactured in Europe
Customer-specific logo and colors

Follow LAPP at:



You can find our terms and conditions
of business at www.lappmobility.com

Lapp Mobility GmbH

Oskar-Lapp-Str. 2 · 70565 Stuttgart · Germany
Phone: +49 711 7838 - 04 · Fax: +49 711 7838 - 3520
www.lappmobility.com · info.de.lmd@lapp.com

