

STANDARD CHARGING CABLE

ITEM NO.: 5555934025 | TYPE 2, MODE 3, 20A, 3-phase, 5m
FOR CHARGING ELECTRIC AND HYBRID CARS



>> THE STANDARD CHARGING CABLE FROM LAPP with a length of 5m enables easy and fast charging at public and private charging stations and wallboxes. Vehicles can be charged with up to 20A 3-phase. The high protection rating of IP 55, together with the additional longitudinal waterproofing, ensures excellent moisture protection. The charging cable, which is designed in accordance to the applicable IEC and EN standards, is both robust and durable, but also easy to handle thanks to its low weight.

TECHNICAL DATA

- Item no.: 5555934025
- Connections:
Type 2 on both sides
- Charging mode:
Mode 3 according to IEC 62196
- Rated current: 20A
- Rated voltage:
440 V AC 3-phase
- Max. Charging power:
11kW
- Permissible temperature range:
-40°C - +50°C
- Cable type:
ÖLFLEX® CHARGE 5G2.5+1x0.5
- Extension length: 5.0 meters
- Protection class IP55 with
additional longitudinal watertightness
- Halogen free
- Flame retardant
- Oil resistant

INCLUDED IN DELIVERY

- Charging cable for public charging stations and wall boxes
- Manual

APPLICABLE STANDARDS

- IEC 61851-1
- IEC 62893-1
- EN 61851-1
- EN 50620
- EN 17186
- 2014/35/EU (Low Voltage Directive),
- 2011/65/EU (RoHS), 215/863/EU