

# STANDARD CHARGING CABLE

ITEM NO.: 5555934032 | TYPE 2, MODE 3, 32A, 3-phase, 10m  
FOR CHARGING ELECTRIC AND HYBRID CARS



**>>> THE STANDARD CHARGING CABLE FROM LAPP** with a length of 10m enables easy and fast charging at public and private charging stations and wallboxes. Vehicles can be charged with up to 32A 3-phase. The high protection rating of IP55, together with the additional longitudinal waterproofing, ensures excellent moisture protection. The charging cable, which is designed in accordance to the applicable IEC and EN standards, is both robust and durable, but also easy to handle thanks to its low weight.

## TECHNICAL DATA

### INCLUDED IN DELIVERY

- Charging cable for public charging stations and wall boxes
- Manual

### APPLICABLE STANDARDS

- IEC 61851-1
- IEC 62893-1
- EN 61851-1
- EN 50620
- EN 17186
- 2014/35/EU (Low Voltage Directive),
- 2011/65/EU (RoHS), 215/863/EU

- Item no.: 5555934032
- Connections: Type 2 on both sides
- Charging mode: Mode 3 according to IEC 62196
- Rated current: 32A
- Rated voltage: 440V AC 3-phase
- Max. Charging power: 22kW
- Permissible temperature range: -40°C - +50°C
- Cable type: ÖLFLEX® CHARGE 5G6+1x0.5
- Extension length: 10 meters
- Protection class IP55 with additional longitudinal watertightness
- Halogen free
- Flame retardant
- Oil resistant